



Main

Range of product	PratiKa Unika
Product or component type	Interlocked socket for container
Device short name	PratiKa Unika socket
Plug, socket category	Low voltage
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

Complementary

Mounting mode	Wall-mounted
[In] rated current	32 A
[Ue] rated operational voltage	400...440 V
Network frequency	50/60 Hz
Ground lug clockwise position	3 h
Plug, socket material	Self-extinguishing engineering polymer housing :
Contacts material	Nickel plated brass pins:
Connections - terminals	Captive screws, completely loosened
Cable cross section	2.5...10 mm ²
Cable entry	Cable gland
Thread type	Pg 21
Product weight	1.156 kg
Colour	Grey (RAL 7035)
Voltage colour	Red

Environment

Standards	EN 60309-1 EN 60309-2
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 62262
Fire resistance	750 °C conforming to IEC 60695-2-1
Relative humidity	50 % (40 °C) 70 % (30 °C)

90 % (20 °C)

Ambient air temperature for operation 35 °C (86400 s)

Contractual warranty

Warranty period 18 months
