

Product data sheet

Specifications



Isoblock interlocked socket - 32 A - 3P + N + E - 380...415 V AC - IP65 - wall

83371

⚠ Discontinued on: May 27, 2019

⚠ Discontinued

Main

Range	PratiKa
Product Or Component Type	Interlocked socket
Device Short Name	Isoblock socket
Plug, Socket Category	Low voltage
Industrial Socket Type	B16
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

Complementary

Mounting Mode	Wall-mounted
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	380...415 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	6 h
Protection Type	Fuse
Fuse Type	Cylindrical
Fuse Size	10.3 x 38 mm
Local Signalling	LED
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Pins: stainless steel Springs: stainless steel
Connections - Terminals	Captive screws
Maximum Cable Cross Section	10 mm²
Maximum Cable Outer Diameter	25 mm
Cable Entry	Cable gland
Thread Type	Pg 21
Net Weight	1.33 kg
Base Dimension	106 x 330 mm
Height	330 mm
Width	106 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	111 mm
Colour	Grey (RAL 7035)
Voltage Colour	Red

Environment

Standards	IEC 60309-1 IEC 60309-2
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to EN 62262
Fire Resistance	850 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	0.1 cm
Package 1 Length	0.2 cm
Package 1 Weight	1 kg

Contractual warranty

Warranty	18 months
----------	-----------