



has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E Taiwan
Load type	Inductive Resistive
Cover plate colour tint	Red

Complementary

Device mounting	Flush Surface
Rated current	15 A at 125 V AC 60 Hz
Number of gangs	2 gangs
Material	Polycarbonate base Polycarbonate cover
Connections - terminals	Screwless terminals
Embedding depth	30 mm
Width	46 mm
Height	70.1 mm
Depth	38.5 mm

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %, non-condensing (storage) 10...95 %, non-condensing (operating)
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	CNS 690 IEC 60364
IP degree of protection	IP20
Standards	CNS 690 IEC 60364

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications