



has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E China
Load type	Resistive
Cover plate colour tint	White

Complementary

Device mounting	Surface Flush
Rated current	16 A at 250 V AC 50/60 Hz
Number of gangs	1 gang
Material	Polycarbonate base Polycarbonate cover
Connections - terminals	Screw terminals
Width	46.7 mm
Height	45.8 mm
Depth	27.28 mm

Environment

Ambient air temperature for storage	0...60 °C
Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %, non-condensing (storage) 10...95 %, non-condensing (operating)
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	GB 2099.1
IP degree of protection	IP20
Standards	GB 2099.1
Product certifications	CCC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications