

Product data sheet

Specifications



250V 20A Taiwan T-Shape 3 Pin Socket 2M Sized Module, White

84426MTE_WE

⚠ Discontinued on: Dec 12, 2016

⚠ Discontinued

Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	2P + E Taiwan
Load Type	Inductive
Cover Plate Colour Tint	White

Complementary

Device Mounting	Surface Flush
Rated Current	20 A at 250 V AC 60 Hz
Number Of Gangs	1 gang
Material	Polycarbonate base Polycarbonate cover
Connections - Terminals	Screw terminals
Width	45.8 mm
Height	46.7 mm
Depth	39 mm

Environment

Ambient Air Temperature For Storage	-5...60 °C
Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	10...95 %, non-condensing (operating) 10...95 %, non-condensing (storage)
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	CNS 690 BS 7671
Ip Degree Of Protection	IP20
Standards	BS 7671 CNS 690

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications