

Product data sheet

Specifications



illuminated selector switch Ø30 - amber- 2 position spring return right to left

9001K34J35LYFA

⚠ Discontinued on: Jul 1, 2020

⚠ Discontinued

Main

| | |
|---------------------------|-----------------------------|
| Range Of Product | Harmony 9001K |
| Product Or Component Type | Illuminated selector switch |
| Device Short Name | 9001K |
| Type Of Operator | Right to left spring return |
| Operator Profile | Amber long handle |

Complementary

| | |
|-------------------------------|------------------------------|
| Bezel Material | Chromium plated metal |
| Mounting Diameter | 30 mm |
| Net Weight | 0.245 kg |
| Shape Of Signaling Unit Head | Octagonal |
| Operator Position Information | 2 positions |
| Contacts Type And Composition | Without contact block |
| Mechanical Durability | 500000 cycles |
| Light Block Supply | Direct |
| Light Source | LED |
| Bulb Base | BA 9s |
| Light Block Colour | Amber |
| [Us] Rated Supply Voltage | 24 V AC/DC |
| Product Compatibility | 9001KA2, mounted side 1 or 2 |
| Device Presentation | Basic element |

Environment

| | |
|---------------------------------------|----------------------------------|
| Protective Treatment | TC |
| Ambient Air Temperature For Storage | -40...70 °C |
| Ambient Air Temperature For Operation | -25...70 °C |
| Electrical Shock Protection Class | Class II conforming to IEC 61140 |
| Ip Degree Of Protection | IP66 conforming to IEC 60529 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------|--|
| Nema Degree Of Protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 |
| Standards | EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 852 JIS C 4520 EN/IEC 60947-1 CSA C22.2 No 14 UL 508 |
| Product Certifications | UL 508 NEMA |
| Vibration Resistance | 7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock Resistance | 50 gn conforming to IEC 60068-2-27 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.572 cm |
| Package 1 Width | 5.334 cm |
| Package 1 Length | 9.144 cm |
| Package 1 Weight | 226.796 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |