



### Main

|                            |  |
|----------------------------|--|
| Range of product           | 9007                                   |
| Series name                | Heavy duty                             |
| Product or component type  | Limit switch head                      |
| Device short name          | 9007C                                  |
| Head type                  | Plunger head                           |
| Product compatibility      | 9007C                                  |
| Associated lever           | 9007C                                  |
| Associated body            | 9007C                                  |
| Movement of operating head | Linear                                 |
| Type of operator           | Steel spring return roller plunger (-) |
| Type of approach           | 2 directions lateral approach          |
| Positive opening           | Without                                |

### Complementary

|                  |             |
|------------------|-------------|
| Switch actuation | By 30° cam  |
| Product weight   | 0.25 lb(US) |

### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | 0...185 °F           |
| Ambient air temperature for storage   | 0...185 °F           |
| Environmental characteristic          | Standard environment |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | Green Premium product   |
| RoHS (date code: YYWW)   | Compliant - since 1150 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                    | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |

---

|                                  |                                       |
|----------------------------------|---------------------------------------|
| Product environmental profile    | Available                             |
| Product end of life instructions | Need no specific recycling operations |

---

**Contractual warranty**

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---