

# Product data sheet

## Characteristics

# 9007EA8M

9007C limit switch lever - zinc - fixed length - outside nylon roller



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007A 9007B 9007C 9007N 9007T10 9007T5
Associated complete product	9007AW 9007C
Movement of operating head	Rotary
Type of operator	Cast zinc spring return 360° adjustable roller lever length: 3 in - offset: - to pass over switch cover
Type of roller	1 nylon outside roller (convertible) diameter: 0.63 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By 30° cam
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

---

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---