



### Main

|                            |   |
|----------------------------|---|
| Range of product           | 9007  |
| Series name                | Heavy duty  |
| Product or component type  | Limit switch head                                       |
| Device short name          | 9007C   |
| Head type                  | Plunger head  |
| Product compatibility      | 9007C   |
| Associated lever           | 9007C   |
| Associated body            | 9007C   |
| Movement of operating head | Linear  |
| Type of operator           | Stainless steel spring return side plunger (adjustable) |
| Type of approach           | 1 direction lateral approach                            |
| Positive opening           | Without   |

### Complementary

|                  |             |
|------------------|-------------|
| Switch actuation | On end      |
| Product weight   | 0.36 lb(US) |

### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | 0...185 °F           |
| Ambient air temperature for storage   | 0...185 °F           |
| Environmental characteristic          | Standard environment |

### Offer Sustainability

|                                  |  |
|----------------------------------|--|
| RoHS (date code: YYWW)           | Will not be compliant<br>Will not be compliant   |
| REACH                            | Reference not containing SVHC above the threshold<br>Reference not containing SVHC above the threshold |
| Product environmental profile    | Available  |
| Product end of life instructions | Need no specific recycling operations  |

Contractual warranty

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---