



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch head
Device short name	9007C
Head type	Multi-directional head
Product compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Multi-directional
Type of operator	Zinc spring return wobble stick without operator (-)
Type of approach	Multi-directional approach multi-directional approach
Positive opening	Without

### Complementary

Switch actuation	Any direction
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	0...185 °F
Ambient air temperature for storage	0...185 °F
Environmental characteristic	Standard environment

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---