



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch head
Device short name	9007C
Head type	Multi-directional head
Product compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Multi-directional
Type of operator	Steel spring return wobble stick (wire extension)
Type of approach	Multi-directional approach multi-directional approach
Positive opening	Without

### Complementary

Switch actuation	Any direction
Product weight	0.57 lb(US)

### Environment

Ambient air temperature for operation	0...185 °F
Ambient air temperature for storage	0...185 °F
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

---

Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---