

Product data sheet

Characteristics

9007LA17

9007C limit switch lever - zinc - 90° fork - RH
opposing nylon rollers



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007C
Associated complete product	9007C
Movement of operating head	Rotary
Type of operator	Cast zinc stay put 90° forked arm with rollers length: 1.5 in - offset: - -
Type of roller	2 nylon RH opposite side roller diameter: 0.75 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By specific cam
Product weight	0.1 lb(US)

Environment

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
