



Main

| | |
|-----------------------------|------------------------------------------------------------------------------------------------------------|
| Range of product | 9007 |
| Series name | Severe duty |
| Product or component type | Limit switch lever |
| Device short name | 9007T/FT |
| Associated head | 9007CS9 9007AS9 9007T5S9 9007T10S9 9007NS9 9007BS9 |
| Associated complete product | 9007FT 9007C..S9 9007T |
| Movement of operating head | Rotary |
| Type of operator | Cast zinc spring return rod lever without rod - offset: - clamp for use with 1/4" key stock (not supplied) |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|--------------------|
| Switch actuation | By any moving part |
| Product weight | 0.1 lb(US) |

Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -10...185 °F |
| Ambient air temperature for storage | -10...185 °F |
| Environmental characteristic | Standard environment |

Offer Sustainability

| | |
|--------------------------|-----------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1150 - Schneider Electric declaration of conformity |

 [Schneider Electric declaration of conformity](#)

| | |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------|
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|