



### Main

|                             |  |
|-----------------------------|--|
| Range of product            | 9007   |
| Series name                 | Severe duty  |
| Product or component type   | Limit switch lever   |
| Device short name           | 9007T/FT   |
| Associated head             | 9007AS9<br>9007T10S9<br>9007CS9<br>9007BS9<br>9007NS9<br>9007T5S9                                  |
| Associated complete product | 9007FT<br>9007C...S9<br>9007T  |
| Movement of operating head  | Rotary   |
| Type of operator            | Cast zinc spring return roller without lever - offset: - roller and clamp only (use 9007R16 or 17) |
| Type of roller              | 1 steel optional position diameter: 1 in - width: 0.25 in  |
| Type of approach            | Lateral approach   |
| Positive opening            | Without  |

### Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight   | 0.1 lb(US) |

### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -10...185 °F         |
| Ambient air temperature for storage   | -10...185 °F         |
| Environmental characteristic          | Standard environment |

### Offer Sustainability

|                        |  |
|------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant<br>Will not be compliant   |
| REACH                  | Reference not containing SVHC above the threshold<br>Reference not containing SVHC above the threshold |

---

|                                  |                                       |
|----------------------------------|---------------------------------------|
| Product environmental profile    | Available                             |
| Product end of life instructions | Need no specific recycling operations |

---

**Contractual warranty**

---

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---