



### Main

Range of product	Flow
Product or component type	Magnetic flowmeter transmitter
Device application	To measure the flow of pressure for liquid, gas, steam
Market segment	Pharmaceutical Power Food and beverage

### Complementary

Communication port protocol	Hart protocol tolerance FOUNDATION fieldbus Modbus
Measurement accuracy	+/- 0.5 % with IMT30A +/- 0.3 % with IMT31A +/- 0.2 % with IMT33A

### Environment

Ambient air temperature for operation	-5...80 °C with hard rubber liner -5...90 °C with polypropylene liner -5...80 °C with polyolefin liner
Product certifications	ATEX IECEX FM CSA NEPSI KTW ACS DVGW WRAS

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins