



⚠ Discontinued

A3031WBP has not been replaced. Please contact your customer care center for more information.

### Main

Range	Kavacha
Product or component type	Bell press switch

### Complementary

Local signalling	LED (grey)
Rated current	6 A at 250 V AC
Width	74 mm
Height	124 mm

### Environment

Environmental characteristic	Weatherproof
IP degree of protection	IP44
Standards	IEC 60529 GB 16915.1 IEC 60669-1

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications