



Main

Range	ZENcelo
Product or component type	Key card switch
Rated current	16 A 240 V AC
Colour tint	White

Complementary

Status LED	LED
Material	Polycarbonate base Polycarbonate grid plate Polycarbonate lenses Polycarbonate surround
Load type	Incandescent 16 A Fluorescent 8 AX Motor 8 A
Device mounting	Surface Flush
Connections - terminals	Brass terminal
Clamping connection capacity	1 x 1...4 x 1 mm ² solid stranded 2 x 2.5 mm ² solid stranded 1 x 1.5...3 x 1.5 mm ² solid stranded
Width	120 mm
Height	70 mm
Depth	40.7 mm

Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	<= 2000 m
Ambient air temperature for storage	0...60 °C

Standards	IEC 60669-2-1
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations