



Main

Range of product	Acti 9
Product name	Acti 9 iPC
Product or component type	Modular socket-outlet
Device short name	IPC
Poles description	2P + E
Outlet standard	German

Complementary

[In] rated current	16 A
[Ue] rated operational voltage	250 V AC 50/60 Hz
Mounting mode	Fixed
Mounting support	Symmetrical DIN rail
9 mm pitches	5
Height	84 mm
Width	45 mm
Depth	63 mm
Net weight	98 g
Colour	White
Local signalling	LED voltage presence indicator light service life: 100000 h
Connections - terminals	Tunnel type terminal1 cable(s) 6 mm ² flexible Tunnel type terminal1 cable(s) 10 mm ² rigid
Wire stripping length	13 mm
Tightening torque	1.2 N.m

Environment

Standards	VDE 0620
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
IK degree of protection	IK03
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------