



Main

Range of product	Acti 9
Product name	Acti 9 iTR
Product or component type	Transformer
Device short name	ITR
Transformer type	Bell transformer

Complementary

[Ue] rated operational voltage	230 V AC 50/60 Hz
Output voltage	8/12 V : +/- 15 % on load 12/16 V : off load
Output short-circuit protection	Built-in
Rated power in VA	4 VA
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	4
Height	89 mm
Width	36 mm
Depth	60 mm
Colour	White
Auxiliary connection terminal	Tunnel type terminals rigid <= 2.5 mm ² Tunnel type terminals flexible <= 2.5 mm ² Tunnel type terminals flexible with ferrule <= 2.5 mm ²
Wire stripping length	6 mm
Tightening torque	0.5 N.m

Environment

Standards	EN 60742 EN 61558-2-6 IEC 61558-2-6
Product certifications	NF
IP degree of protection	IP20 conforming to IEC 60529
Overvoltage category	Class II with terminal shields in option

Ambient air temperature for operation	-20...55 °C
Ambient air temperature for storage	-25...80 °C

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1312 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
