



Main

Range of product	Acti 9
Product or component type	Double OC or fault contact
Device short name	IOF/SD+OF
Signal contacts composition	2 C/O
[In] rated current	1 A at 130 V DC 1.5 A at 60 V DC 2 A at 48 V DC 6 A at 24 V DC 3 A at 415 V AC - 50/60 Hz 6 A at 240 V AC - 50/60 Hz
9 mm pitches	1

Complementary

Range compatibility	Acti 9 iC60 Acti 9 iDPN Vigi Acti 9 iID Acti 9 iSW-NA Acti 9 iC60 RCBO Acti 9 iC65 Acti 9 ARA Acti 9 RCA Acti 9 iDPN (China version) Acti 9 iC40
[Ui] rated insulation voltage	4 kV
Local signalling	Mechanical indicator
Mounting mode	Fixed
Mounting support	DIN rail
Height	90 mm
Width	9 mm
Depth	73 mm
Product weight	43 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White
Connections - terminals	Screw clamp terminal 2 cable(s) 2.5 mm ² rigid Screw clamp terminal 1 cable(s) 0.5...2.5 mm ² flexible Screw clamp terminal 1 cable(s) 1...4 mm ² rigid Screw clamp terminal 2 cable(s) 1.5 mm ² flexible with ferrule
Wire stripping length	10 mm
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1216 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information

Contractual warranty

Warranty period	18 months
-----------------	-----------