

# Product data sheet

Specifications



shunt trip release with OC contact,  
Acti9, iMX+OF, voltage release, 48  
V AC

A9A26947

## Main

Range Of Product	Acti9
Product Or Component Type	Shunt trip release with OC contact
Device Short Name	iMX+OF
Signal Contacts Composition	1 C/O
[In] Rated Current	AC-12 2 A at 48 V, AC 50 Hz DC-12 2 A at 48 V, DC
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 48 V DC
9 Mm Pitches	2

## Complementary

Range Compatibility	Acti 9 Acti9 iC65 Acti 9 Acti9 ARA Acti 9 Acti9 iDPN Vigi Acti 9 Acti9 iLD Acti 9 Acti9 iSW-NA Acti 9 Acti9 RCA Acti 9 Acti9 iDPN (China version) Acti 9 Acti9 iC60 double terminals miniature circuit breaker Acti 9 Acti9 iC40
Local Signalling	Action indicator
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Width	18 mm
Colour	White
Connections - Terminals	Clamp terminal - 1 cable(s) 5 mm² - rigid Clamp terminal - 2 cable(s) 2.4 mm² - rigid Clamp terminal - 1 cable(s) 3 mm² - flexible Clamp terminal - 2 cable(s) 2.4 mm² - flexible with cable end
Tightening Torque	1 N.m
Compatibility Code	IMX+OF

## Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-35...70 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-40...85 °C
-------------------------------------	-------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	7.900 cm
Package 1 Length	9.300 cm
Package 1 Weight	80.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	26.500 cm
Package 2 Weight	700.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.783 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>