

# Product data sheet

Specifications



## Acti9 centralized control iATLc

A9C15404

### Main

Range Of Product	Acti9
Device Short Name	iATLc
Product Or Component Type	Centralized control auxiliary
[Uc] Control Circuit Voltage	24...240 V AC 50/60 Hz impulse

### Complementary

[Ui] Rated Insulation Voltage	440 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Remote Control Type	2 entries for switch
Mounting Mode	Fixed, on right side of TL
Mounting Support	DIN rail
9 Mm Pitches	1
Height	81 mm
Width	9 mm
Depth	69 mm
Colour	White
Connections - Terminals	Tunnel type terminals0.5...4 mm² - rigid Tunnel type terminals0.5...4 mm² - rigid - with cable end Tunnel type terminals1...4 mm² - flexible Tunnel type terminals1...4 mm² - flexible - with cable end
Wire Stripping Length	11 mm
Tightening Torque	1 N.m
Range Compatibility	Acti 9 Acti9 iTL iTL Acti 9 Acti9 iTL iTLi Acti 9 Acti9 iTL iTLs
Product Compatibility	ITL (32 A) ITL (16 A)

### Environment

Overvoltage Category	III
Ip Degree Of Protection	IP20 conforming to IEC 60529
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-40...70 °C
Standards	EN/IEC 60669-2-2

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8 cm
Package 1 Width	2.4 cm
Package 1 Length	9.4 cm
Package 1 Weight	40 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.5 cm
Package 2 Width	9.5 cm
Package 2 Length	26.5 cm
Package 2 Weight	534 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	4.76 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations