



Main

Device application	Control Distribution
Range	Acti 9
Product name	Reflex iC60
Device short name	Reflex iC60N
Product or component type	Integrated control circuit breaker
Poles description	3P
Number of protected poles	3
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C

Complementary

[In] rated current	25 A
Network frequency	50/60 Hz
Breaking capacity code	N
Breaking capacity	Icu 20 kA at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 Icu 10 kA at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC
Contact position indicator	Yes
Control type	Remote control by continuous command Remote control by pulse Toggle ON/OFF button
Control signal type	Impulse Maintained
Local signalling	Red LED: fault Flashing LED: device overheat Flashing LED: device ready Flashing LED: device tripped

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Green LED: device ON

[Uc] control circuit voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 24 V DC 48 V AC 50/60 Hz 48 V DC
[Us] rated supply voltage	230 V AC 50/60 Hz
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	11
Height	84 mm
Width	99 mm
Depth	77 mm
Colour	White
Mechanical durability	50000 cycles
Electrical durability	AC-1 : 50000 cycles AC 50 Hz
Provision for padlocking	Padlockable
Locking options description	Padlock in OFF position
Earth-leakage protection	Separate block
Product compatibility	Without PLC

Environment

IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3
Tropicalisation	2
Relative humidity	93 % (40 °C)

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1329 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------