

# Product data sheet

Specifications



## Acti9 iPB 1NC single push button grey - indicator light red 110-230Vac

A9E18037

### Main

Range Of Product	Acti9
Product Name	Acti9 iPB
Product Or Component Type	Push-button
Device Short Name	iPB
Standards	IEC 60947-5-1 IEC 60669-1

### Complementary

Contacts Type And Composition	1 NC
[Ie] Rated Operational Current	20 A
[Ue] Rated Operational Voltage	250 V AC
Control Type	1 push-button grey
Local Signalling	LED indicator red, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Signalling Circuit Voltage	AC: 110...230 V 50/60 Hz
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: Clario Upside: Libro Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical Durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - Terminals	Staggered tunnel terminal1 cable(s) 0.5 mm² rigid Staggered tunnel terminal1 cable(s) 0.5 mm² flexible Staggered tunnel terminal1 cable(s) 0.5 mm² flexible with ferrule Staggered tunnel terminal2 cable(s) 2.5 mm² rigid Staggered tunnel terminal2 cable(s) 2.5 mm² flexible Staggered tunnel terminal2 cable(s) 2.5 mm² flexible with ferrule
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...80 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	2.000 cm
Package 1 Length	8.000 cm
Package 1 Weight	45.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.000 cm
Package 2 Width	10.000 cm
Package 2 Length	23.000 cm
Package 2 Weight	599.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.972 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts & Cables Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations