



Main

Range of product	Acti 9
Product name	Acti 9 iIL
Product or component type	Modular pilot lighth
Device short name	IIL
[Us] rated supply voltage	110...130 V DC 110...230 V AC 50/60 Hz

Complementary

Flashing frequency	2 Hz
Indicator light	1 LED blue, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Mounting mode	Fixed
Mounting support	Symmetrical DIN rail
Comb busbar and distribution block compatibility	Upside : ProDis
9 mm pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary connection terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm ² Tunnel type terminal 2 cable(s) rigid 2.5 mm ² Tunnel type terminal 1 cable(s) flexible 0.5 mm ² Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm ² Tunnel type terminal 2 cable(s) flexible 2.5 mm ²
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Standards	IEC 60947-5-1
IP degree of protection	IP2

IPxx B

Pollution degree	3
Tropicalisation	2
Relative humidity	95 % (55 °C)
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...80 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1001 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------