



Main

| | |
|---------------------------|---|
| Range of product | Acti 9 |
| Product name | Acti 9 iIL |
| Product or component type | Modular pilot lighth |
| Device short name | IIL |
| [Us] rated supply voltage | 110...130 V DC 110...230 V AC 50/60 Hz |

Complementary

| | |
|--|---|
| Flashing frequency | 2 Hz |
| Indicator light | 1 LED yellow, service life 100000 h of constant lighting efficiency (consumption 0.3 W) |
| Mounting mode | Fixed |
| Mounting support | Symmetrical DIN rail |
| Comb busbar and distribution block compatibility | Upside : ProDis |
| 9 mm pitches | 2 |
| Height | 82 mm |
| Width | 18 mm |
| Depth | 69.5 mm |
| Colour | White (RAL 9003) |
| Auxiliary connection terminal | Tunnel type terminal 1 cable(s) rigid 0.5 mm ² Tunnel type terminal 2 cable(s) rigid 2.5 mm ² Tunnel type terminal 1 cable(s) flexible 0.5 mm ² Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm ² Tunnel type terminal 2 cable(s) flexible 2.5 mm ² |
| Wire stripping length | 9 mm |
| Tightening torque | 1 N.m |

Environment

| | |
|-----------|---------------|
| Standards | IEC 60947-5-1 |
|-----------|---------------|

| | |
|---------------------------------------|----------------|
| IP degree of protection | IP2 IPxx B |
| Pollution degree | 3 |
| Tropicalisation | 2 |
| Relative humidity | 95 % (55 °C) |
| Ambient air temperature for operation | -35...70 °C |
| Ambient air temperature for storage | -40...80 °C |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1001 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available Product Environmental Profile |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|