



ⓘ Discontinued

Main

Range of product	Acti 9
Product name	Acti 9 iPRD
Product or component type	Surge arrester with pluggable cartridge
Device short name	IPRD
Device application	Distribution
Poles description	3P
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network
Earthing system	IT

Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV
[Ue] rated operational voltage	230 V AC (+/- 10 %) at 50/60 Hz 400 V AC (+/- 10 %) at 50/60 Hz
[In] nominal discharge current	Common mode: 5 kA (L/PE) Common mode: 5 kA (N/PE)
[Imax] maximum discharge current	Common mode: 20 kA L/PE
[Uc] maximum continuous operating voltage	Common mode: 460 V L/PE
Maximum [Up] voltage protection level	Common mode <1.5 kV type 2 L/PE
Disconnecter device type	Associated circuit breaker iC60N 25 A curve C - Icu 10 kA Associated circuit breaker iC60H 25 A curve C - Icu 15 kA Associated circuit breaker iC60L 25 A curve C - Icu 25 kA
Signalling circuit voltage	0.25 A/250 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	6

Height	81 mm
Width	54 mm
Depth	69 mm
Colour	White (RAL 9003)
Response time	<= 25 ns
Connections - terminals	Tunnel type terminal (downside) 2.5...35 mm ² Tunnel type terminal (upside) 2.5...35 mm ²
Tightening torque	2.5 N.m

Environment

Standards	EN 61643-11 IEC 61643-11
Product certifications	CE
IP degree of protection	IP40 on front face: conforming to IEC 60529 IP20 built-in: conforming to IEC 60529
IK degree of protection	IK03 conforming to IEC 62262
Relative humidity	5...90 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

A9L16573 is replaced by:



Surge arresters A9L20321

iPRD20r modular surge arrester - 3P - IT - 460V - with remote transfert

Qty 1

Reason for Substitution: End of life | Substitution date: 22 November 2017