



has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Product or component type	Cartridge
Device short name	C40-600 PV
Surge arrester type	Electrical distribution network

### Complementary

Surge arrester class type	Type 2
Surge arrester technology	MOV
[Ue] rated operational voltage	600 V DC
Nominal discharge current	15 kA
Maximum discharge current	40 kA
[Uc] maximum continuous operating voltage	340 V
Maximum [Up] voltage protection level	<1.4 kV type 2
Local signalling	White/red flag
Mounting mode	Plug-in
Mounting support	Into SPD module
9 mm pitches	2
Height	50 mm
Width	18 mm
Depth	60 mm
Colour	White (RAL 9003)
Material	PBT (polybutylene terephthalate)
Response time	< 25 ns

### Environment

Standards	EN 61643-11 IEC 61643-1
IP degree of protection	IP20 front face:
Relative humidity	5...90 %
Operating altitude	0...2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

Contractual warranty

---

Warranty	18 months
----------	-----------

---