



### Main

Range	Prodis
Product or component type	Add-on residual current devices
Device short name	Vigi TG60
Poles description	4P
[In] rated current	63 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Selective
Earth-leakage protection class	Type A-SI

### Complementary

Device location in system	Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	400 V AC 50 Hz phase to phase
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	440 V AC 50 Hz conforming to EN 61009-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN 61009-1
Local signalling	ON/OFF indication
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws
9 mm pitches	6
Height	82 mm
Width	54 mm
Depth	70 mm
Net weight	210 g
Colour	White

Connections - terminals	Cable upstream 0.75...16 mm <sup>2</sup> rigid Cable upstream 0.33...10 mm <sup>2</sup> flexible
Wire stripping length	13 mm
Tightening torque	2 N.m

## Environment

Standards	IEC 60947-2 EN 61009-1 EN 61009-2-1
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN 61009-1
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...60 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------