



Main

Range of product	Prodis Librio Clario Acti 9
Product or component type	Shunt trip release
Device short name	MX
[Uc] control circuit voltage	100...415 V AC 50/60 Hz 110...130 V DC
9 mm pitches	2

Complementary

Range compatibility	Acti 9 iDPN Acti 9 C120 Acti 9 C40 Acti 9 C60H-DC Acti 9 C60NA-DC Acti 9 C60PV-DC Acti 9 DPN Vigi Acti 9 DT40 Acti 9 DT60 Acti 9 ID C40 Acti 9 IDc Acti 9 ITG40 Acti 9 ID Acti 9 SW60-DC
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net weight	60 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm ² - flexible

Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm² - flexible with ferrule
Screw clamp terminal (bottom) - 1 cable(s) 0.5...2.5 mm² - rigid

Wire stripping length	9 mm for bottom connection
Tightening torque	1 N.m bottom
Compatibility code	MX

Environment

Standards	EN/IEC 60947-5-1
Product certifications	KEMA ASEFA LCIE ASTA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------