

# Product data sheet

Specifications



## MX Shunt trip 415Vac 110-130Vdc

A9N26476

### Main

Range Of Product	Acti9
Product Or Component Type	Shunt trip release
Device Short Name	MX
[Uc] Control Circuit Voltage	100...415 V AC 50/60 Hz 110...130 V DC
9 Mm Pitches	2

### Complementary

Range Compatibility	Acti 9 Acti9 iDPN Acti 9 Acti9 C120 Acti 9 Acti9 C40 Acti 9 Acti9 C60H-DC Acti 9 Acti9 C60NA-DC Acti 9 Acti9 C60PV-DC Acti 9 Acti9 DPN Vigi Acti 9 Acti9 DT40 Acti 9 Acti9 DT60 Acti 9 Acti9 ID C40 Acti 9 Acti9 IDc Acti 9 Acti9 ITG40 Acti 9 Acti9 ID Acti 9 Acti9 SW60-DC
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net Weight	60 g
Colour	White
Connections - Terminals	Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm² - flexible Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm² - flexible with ferrule Screw clamp terminal (bottom) - 1 cable(s) 0.5...2.5 mm² - rigid
Wire Stripping Length	9 mm for bottom connection
Tightening Torque	1 N.m bottom
Compatibility Code	MX

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN/IEC 60947-5-1
Product Certifications	KEMA ASEFA LCIE ASTA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	8 cm
Package 1 Length	9.5 cm
Package 1 Weight	69 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	10 cm
Package 2 Width	9 cm
Package 2 Length	27 cm
Package 2 Weight	598 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.062 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>