

Product data sheet

Specifications

Category5e, 25pr UTP Cable 305m/ reel White, LSZH



ACT25P5EULS3RWE

⚠ Discontinued on: Dec 17, 2020

⚠ Discontinued

Main

Range	Actassi
Product Or Component Type	Copper cable
Colour Tint	White
Cable Shielding Type	U/UTP

Complementary

Type Of Cable	Multipair cable
Communication Network Category	5e
Maximum Loop Resistance	93.8 Ohm
Capacitance Unbalance	330 pF / 100 m
Maximum Resistance Unbalance	5 %
Nominal Velocity Propagation	65 %
Wire Insulation Material	PE
Awg Gauge	AWG 24
Cable Outer Diameter	12.5 mm
Cable Length	305 m
Cable Weight	184 kg

Environment

Ambient Air Temperature For Operation	-20...60 °C
Flame Retardance	LSZH

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	43 cm
Package 1 Width	63 cm
Package 1 Length	63 cm
Package 1 Weight	65500 g

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months