



Main

Range	Actassi
Product	Patch cord
Colour	Blue
Cable shielding type	FTP

Complementary

Rated voltage	150 V AC
[In] rated current	1.5 A
Insulation resistance	1 MOhm
Cable length (customisable value in configurator)	0...2 m
Communication network category	5e
Contacts material	Phosphor bronze with 50 micro-inches gold over 100 micro-inches nickel
Contact resistance	10 mOhm
AWG	AWG 26
Number of matings	>= 1000 cycles
Targeted region	Asia Pacific

Environment

Flame retardance	CM
Standards	IEC 60603-7 AS/NZS 3080:2003 FCC part 68 subpart F

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1301 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
