

# Product data sheet

Specifications

## Actassi Unitube Non-Armoured Fibre Cable OM2 8-Core HDPE



ACTUDUTNA08MM5

 **Discontinued on:** Jun 30, 2021

 **Discontinued**

### Main

Range	Actassi
Product	Fibre optic cable multi mode
Device Application	Communication
Cable Packaging	Reel

### Complementary

Maximum Attenuation	3.5 dB / 1 km at 850 nm 1.5 dB / 1 km at 1300 nm
Fibre Performance	OM2 50/125 µm
Optic Fibre Type	Loose tube diameter: 250 µm
Type Of Cable	Unitube non armoured
Numerical Aperture	0.2 +/- 0.015
Number Of Optic Fibre	8
Bending Radius	10 x overall diameter long term 20 x overall diameter short term
Pulling Force	660 N installed 200 N operation
Colour	Sheath: black
Type Of Installation	Outdoor
Cabling Installation System	Cable duct
Diameter	8.0 mm cable +/- 0.2 mm 9 mm cable +/- 0.2 mm
Cable Weight	77 kg / 1000 m
Targeted Region	Asia Pacific.

### Environment

Ambient Air Temperature For Operation	-40...70 °C
Environmental Characteristic	UV and water resistant: HDPE (high-density polyethylene)

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	139 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations