

Product data sheet

Characteristics

AJ1

L100/300 limit switch lever - aluminum - fixed length - center steel roller



Main

| | |
|-----------------------------|--|
| Range of product | L100/300 |
| Series name | Severe duty |
| Product or component type | Limit switch lever |
| Device short name | L100/300 |
| Associated complete product | HL100 HL300 HML100 HML300 L100 L300 ML100 ML300 |
| Movement of operating head | Rotary |
| Type of operator | Aluminium spring return roller lever length: 2.25 in - offset: - - |
| Type of roller | 1 steel center roller diameter: 1 in - width: 0.25 in |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight | 0.1 lb(US) |

Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -10...185 °F |
| Ambient air temperature for storage | -10...185 °F |
| Environmental characteristic | Standard environment |

Offer Sustainability

| | |
|-------------------------------|--|
| RoHS (date code: YYWW) | Will not be compliant Will not be compliant |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |

| | |
|----------------------------------|---------------------------------------|
| Product end of life instructions | Need no specific recycling operations |
|----------------------------------|---------------------------------------|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
