

Product data sheet

Specifications



Plug outlet, Linergy HK, 3P+Nc,
16A, 2 points, cable length 200

AK5PC131

Main

Range	Linergy
Product Name	HK
Product Or Component Type	Plug outlet
Poles Description	3P + Nc
[Ith] Conventional Free Air Thermal Current	10 A common mode 16 A
I²T On Activation	100000 A².s
Number Of Points	2
Number Of Cables	1 cable(s) 1.5 mm² 3 cable(s) 2.5 mm²
Cable Length	0.2 m
Quantity Per Set	Set of 6

Complementary

[Ui] Rated Insulation Voltage	600 V conforming to CSA 600 V conforming to UL 690 V conforming to IEC 60439-1
Peak Current	25 kA
Electrical Connection	Connector
Width	36 mm
Height	46 mm
Depth	38 mm
Net Weight	0.045 kg

Environment

Standards	IEC 60439
Product Certifications	DNV LROS (Lloyds register of shipping) UL CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	13.0 cm
Package 1 Length	15.5 cm
Package 1 Weight	54.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	12.5 cm
Package 2 Width	13.0 cm
Package 2 Length	15.5 cm
Package 2 Weight	391.0 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	90
Package 3 Height	30.0 cm
Package 3 Width	40.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	7.06 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)