



### Overview

Model Name	APC 17" Rack LCD Console - China
Includes	C13-C14 power cord , Country-specific detachable power cord , Documentation CD , Firmware upgrade cable , Installation guide , Single user rack mount kit , USB KVM cable
Standard Lead Time	Usually in Stock
Product Distribution	China

### Input

Nominal Input Voltage	100V , 240V
Input Frequency	50/60 Hz

### Supported Hardware

Panel Size	17
Pixel Pitch	0.26
Display Colors	16
Trackball Type	PS/2 Touchpad , USB mouse
LCD Power Consumption	19 W

### Physical

Net Weight	15.9 kg
Maximum Height	44.0 mm
Maximum Width	482.0 mm
Maximum Depth	614.0 mm
Shipping Weight	19.46 kg
Shipping Height	152.0 mm
Shipping Width	673.0 mm
Shipping Depth	826.0 mm
Minimum Mounting Depth	26.77
Maximum Mounting Depth	41.33
Rack Height	1 U
Color	Black

## Environmental

Operating Environment	0 - 40 °C
Operating Elevation	0-600 meters

## Conformance

Approvals	CCC
Standard warranty	2 years repair or replace

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs