

Product data sheet

Characteristics

AP6020A

Rack PDU, Basic, 0U/1U, 100-240V/20A,
220-240V/16A, (13) C13



Overview

| | |
|----------------------|--|
| Model Name | Rack PDU, Basic, 0U/1U, 100-240V/20A, 220-240V/16A, (13) C13 |
| Includes | Installation guide |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Afghanistan |

Output

| | |
|--------------------------------------|-----------------------------------|
| Maximum Total Current Draw per Phase | 20 A |
| Output Connections | (13) IEC 320 C13 (Battery Backup) |

Input

| | |
|--|-------------|
| Nominal Input Voltage | 100V |
| Input Frequency | 50/60 Hz |
| Regulatory Derated Input Current (North America) | 16 A |
| Input Connections | IEC-320 C20 |
| Acceptable Input Voltage | 100-240 VAC |
| Maximum Line Current per phase | 20 A |
| Maximum Input Current per phase | 20 A |
| Load Capacity | 3300 VA |

Physical

| | |
|-----------------|----------|
| Net Weight | 1.5 kg |
| Maximum Height | 388.0 mm |
| Maximum Width | 44.0 mm |
| Maximum Depth | 93.0 mm |
| Shipping Weight | 2.02 kg |
| Shipping Height | 436.0 mm |
| Shipping Width | 210.0 mm |
| Shipping Depth | 76.0 mm |
| Color | Black |

Conformance

| | |
|-------------------|---------------------------|
| Approvals | CE |
| Standard warranty | 2 years repair or replace |

Sustainable Offer Status

| | |
|-------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |
