



Overview

| | |
|----------------------|---|
| Model Name | Rack PDU, Metered, 2U, 100V, (16) 5-15 |
| Includes | Cord retention bracket(s) , Installation guide , Rack Mounting brackets , User Manual |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Japan |

Output

| | |
|--------------------------------------|----------------------------------|
| Nominal Output Voltage | 100V |
| Maximum Total Current Draw per Phase | 30 A |
| Output Connections | (16) NEMA 5-15R (Battery Backup) |
| Overload Protection | Yes |

Input

| | |
|--------------------------------|--------------|
| Nominal Input Voltage | 100V 120V |
| Input Frequency | 50/60 Hz |
| Input Connections | NEMA L5-30P |
| Cord Length | 3.66 meters |
| Number of Power Cords | 1 |
| Maximum Line Current per phase | 30 A |
| Load Capacity | 3000 VA |

Physical

| | |
|-----------------|----------|
| Net Weight | 3.36 kg |
| Maximum Height | 88.0 mm |
| Maximum Width | 444.0 mm |
| Maximum Depth | 112.0 mm |
| Shipping Weight | 5.41 kg |
| Shipping Height | 140.0 mm |
| Shipping Width | 508.0 mm |
| Shipping Depth | 368.0 mm |

Environmental

| | |
|-----------------------------|----------------|
| Operating Environment | -5 - 45 °C |
| Operating Relative Humidity | 5 - 95 % |
| Operating Elevation | 0-3000 meters |
| Storage Temperature | -25 - 65 °C |
| Storage Relative Humidity | 5 - 95 % |
| Storage Elevation | 0-15000 meters |

Conformance

| | |
|-------------------|---------------------------|
| Approvals | METI Denan , VCCI |
| Standard warranty | 2 years repair or replace |

Sustainable Offer Status

| | |
|-------------------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |
| Battery Directive | Compliant |