



Overview

Model Name	Rack PDU, Metered, 2U, 30A, 208V, (12) C13s & (4) C19
Includes	Cord retention bracket(s) , Installation guide , Rack Mounting brackets , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Grenada , Guadeloupe , Guatemala , Guyana , Haiti , Honduras , Jamaica , Japan , Martinique , Mexico , Netherlands Antilles , Nicaragua , Panama , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	208V
Maximum Total Current Draw per Phase	24 A
Output Connections	(12) IEC 320 C13 (Battery Backup) , (4) IEC 320 C19 (Battery Backup)
Overload Protection	Yes

Input

Nominal Input Voltage	200V 208V 230V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	24 A
Input Connections	NEMA L6-30P
Cord Length	3.66 meters
Number of Power Cords	1
Maximum Input Current per phase	30 A
Load Capacity	4992 VA

Physical

Net Weight	3.36 kg
Maximum Height	88.0 mm

Maximum Width	444.0 mm
Maximum Depth	112.0 mm
Shipping Weight	5.42 kg
Shipping Height	140.0 mm
Shipping Width	508.0 mm
Shipping Depth	368.0 mm

Environmental

Operating Environment	-5 - 45 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	CSA , FCC Part 15 Class A , ICES-003 , PSE , UL 60950 , UL Listed , cUL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant