

AP9510520

MasterSwitch Pwr Recept, 2U, 20A, 120V, (2)5-20



AP9510520 has not been replaced. Please contact your customer care center for more information.

Overview

Model Name	MasterSwitch Pwr Recept, 2U, 20A, 120V, (2)5-20
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Brazil , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , Haiti , Honduras , Jamaica , Martinique , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , Turks And Caicos Islands , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	20 A
Output Connections	(2) NEMA 5-20R (Battery Backup)
Overload Protection	No

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-20P
Cord Length	3.05 meters
Number of Power Cords	1
Acceptable Input Voltage	120 VAC
Maximum Line Current per phase	16 A
Maximum Input Current per phase	16 A
Load Capacity	1920 VA

Physical

Net Weight	1.91 kg
Maximum Height	84.0 mm
Maximum Width	140.0 mm

Maximum Depth	84.0 mm
Shipping Weight	2.27 kg
Shipping Height	331.0 mm
Shipping Width	140.0 mm
Shipping Depth	178.0 mm
Color	Beige

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 65 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-9000 meters

Conformance

Approvals	CSA , CSA 22.2 No. 950 , UL 1950 , UL Listed
Standard warranty	2 years repair or replace
Equipment protection policy	--