

# Product data sheet

Specifications



## DIALBOARD 3H4L/FRONT PANE

APD1B34

⚠ Discontinued on: Jan 22, 2021

⚠ Discontinued

### Main

Enclosure Name	Dialboard
Product Or Component Type	Dialboard front panels
Range Of Product	Tego Dial

### Complementary

Colour Code	RAL 7016
Colour	Grey
Depth	999 mm
Fixing Mode	By clamp
Height Pitches Number	3
Material	Aluminium PC Polyurethane
Maximum Load	25 kg
Net Weight	0.6 kg
Type Of Paint	Textured Polyester powder
Width Pitches Number	4

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Product Certifications	UL CSA BV
Environmental Characteristic	Standard ambiance
Ik Degree Of Protection	IK09
Ip Degree Of Protection	IP55 conforming to IEC 529
Protective Treatment	TC
Resistance To Incandescent Wire	960 °C conforming to IEC 695-2-1
Shock Resistance	15 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 68-2-27
Ambient Air Temperature For Storage	-25...55 °C
Vibration Resistance	0.7 gn (f = 5...100 Hz)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------