

Product data sheet

Specifications

Tego Dial range



DIALMOVE PROFILE L1250MM

APD1M125L

⚠ Discontinued on: Jan 22, 2021

⚠ Discontinued

Main

| | |
|-------------------------------------|---------------|
| Accessories Included With Enclosure | Straight tube |
| Quantity Per Set | Set of 5 |
| Range Of Product | Tego Dial |

Complementary

| | |
|--------------------------------------|---|
| Cable Outer Diameter | 13 mm |
| Colour Code | RAL 7016 |
| Colour | Grey |
| Length | 1250 mm |
| Material | ABS (acrylonitrile butadiene-styrene) Aluminium NBR 50-60 SHORE |
| Maximum Room For Connectors | 60 x 25 mm |
| Number Of Cables | 4 |
| Permanent Permissible Load | 30 kg |
| Maximum Permissible Distance Of Load | 1600 mm |
| Net Weight | 10.6 kg |
| Type Of Paint | Tinted throughout Polyester powder |

Environment

| | |
|-------------------------|--|
| Product Certifications | BV |
| Ip Degree Of Protection | IP44 conforming to NF C 20-010 IP55 conforming to NF C 20-010 |
| Protective Treatment | TC |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications