

# Product data sheet

Specifications

## Tego Dial range



## DIALPACK 3H4L/ENCLOSURE

APD1P34

⚠ Discontinued on: Jan 22, 2021

⚠ Discontinued

### Main

Closing Element Type	1/4-turn device with stop
Enclosure Name	Dialpack
Product Or Component Type	Dialpack control consoles
Range Of Product	Tego Dial

### Complementary

Colour Code	RAL 7016
Colour	Grey
Depth	150 mm
Fixing Mode	By drilled
Height Pitches Number	3
Type Of Keylock	Ronis
Key Number	455
Material	Sheet steel
Maximum Load	25 kg
Opening Door Holder	120
Opening Mechanism	Hinged
Net Weight	3.3 kg
Maximum Thermal Resistance	50 W
Type Of Paint	Textured Polyester powder
Width Pitches Number	4

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Product Certifications	CSA BV UL
Environmental Characteristic	Standard ambience
Ik Degree Of Protection	IK09
Ip Degree Of Protection	IP65 conforming to IEC 529
Protective Treatment	TC

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Resistance To Incandescent Wire	960 °C conforming to IEC 695-2-1
Shock Resistance	15 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 68-2-27
Ambient Air Temperature For Storage	-25...55 °C
Vibration Resistance	0.7 gn (f = 5...100 Hz)

## Contractual warranty

Warranty	18 months
----------	-----------