

Product data sheet

Characteristics

APN

L100/300 limit switch lever - aluminum - fixed length - center nylon roller



Main

Range of product	L100/300
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	L100/300
Associated complete product	HL100 HL300 HML100 HML300 L100 L300 ML100 ML300
Movement of operating head	Rotary
Type of operator	Aluminium spring return roller lever length: 5 in - offset: - -
Type of roller	1 nylon center roller diameter: 0.75 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Product weight	0.1 lb(US)

Environment

Ambient air temperature for operation	-10...185 °F
Ambient air temperature for storage	-10...185 °F
Environmental characteristic	Standard environment

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------
