

AR2401

NetShelter SV 42U 600mm Wide x 1060mm Deep Enclosure without Sides Black



Overview

| | |
|----------------------|---|
| Description | Universal IT enclosure provided with no side panels for spaces that require less security at the rack or will be paired with other enclosures to form a row and position side panels only at the row ends. The enclosure is for low to medium density server and networking applications. Compact width to optimize data center space. 42U height to easily roll through doorways. |
| Model Name | NetShelter SV 42U 600mm Wide x 1060mm Deep Enclosure without Sides Black |
| Includes | Baying hardware , Door key , Doors , Leveling feet , Mounting Hardware , Pre-installed casters , Qty 4 - Bolt-down brackets , Roof , Unpacking sheet |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Afghanistan , Albania , Algeria , Andorra , Angola , Anguilla , Antigua And Barbuda , Argentina , Armenia , Aruba , Australia , Austria , Azerbaijan , Bahamas , Bahrain , Bangladesh , Barbados , Belarus , Belgium , Belize , Benin , Bermuda , Bhutan , Bolivia , Bosnia And Herzegovina , Botswana , Brazil , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Canada , Cayman Islands , Central African Republic , Chad , Chile , China , Colombia , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Costa Rica , Cote D'Ivoire , Croatia , Cuba , Cyprus , Czech Republic , Denmark , Djibouti , Dominica , Dominican Republic , East Timor , Ecuador , Egypt , El Salvador , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Falkland Islands (Malvinas) , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Grenada , Guadeloupe , Guatemala , Guinea , Guyana , French Guiana , Haiti , Honduras , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jamaica , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Mexico , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , Netherlands Antilles , New Zealand , Nicaragua , Niger , Nigeria , Norway , Oman , Pakistan , Panama , Papua New Guinea , Paraguay , Peru , Philippines , Poland , Portugal , Puerto Rico , Reunion , Romania , Russian Federation , Rwanda , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Taiwan , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Trinidad And Tobago , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , United States , Uruguay , Uzbekistan , Venezuela , Viet Nam , VIRGIN ISLANDS (UNITED STATES) , Western Sahara , Yemen , Zambia , Zimbabwe |

Physical

| | |
|-----------------|-----------|
| Net Weight | 85.0 kg |
| Maximum Height | 2057.0 mm |
| Maximum Width | 600.0 mm |
| Maximum Depth | 1060.0 mm |
| Shipping Weight | 102.3 kg |

| | |
|------------------------|-----------|
| Shipping Height | 2181.0 mm |
| Shipping Width | 700.0 mm |
| Shipping Depth | 1160.0 mm |
| Minimum Mounting Depth | 6.6 |
| Maximum Mounting Depth | 30.6 |
| Rack Height | 42 U |
| Color | Black |
| Vertical Posts | 18 gauge |
| Front Door | 16 gauge |
| Rear Door | 16 gauge |
| Roof | 19 gauge |
| EIA Mounting Rails | 15 gauge |
| Side Panels | 18 gauge |

Conformance

| | |
|-------------------|--------------------------|
| Approvals | UL 2416 , UL 60950-1 |
| Standard warranty | 5 year repair or replace |

Sustainable Offer Status

| | |
|-------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |