



Overview

Description	Deep and Tall Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Tall to provide 48U spaces for environments that can take advantage of higher spaces and provide more mounting u-spaces at each enclosure footprint. Compact width to optimize data center space.
Model Name	NetShelter SV 48U 600mm Wide x 1200mm Deep Enclosure with Sides Black
Includes	Baying hardware
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan

Physical

Net Weight	131.2 kg
Maximum Height	2324.0 mm
Maximum Width	600.0 mm
Maximum Depth	1200.0 mm
Shipping Weight	151.7 kg
Shipping Height	2448.0 mm
Shipping Width	700.0 mm
Shipping Depth	1300.0 mm
Minimum Mounting Depth	6.6
Maximum Mounting Depth	36.1
Rack Height	48 U
Color	Black
Vertical Posts	18 gauge
Front Door	16 gauge
Rear Door	16 gauge
Roof	19 gauge
EIA Mounting Rails	14 gauge
Side Panels	18 gauge

Conformance

Approvals	UL 2416
-----------	---------

Standard warranty	5 year repair or replace
-------------------	--------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
