

AR4018IA

NetShelter CX 18U Secure Soundproof Server Room in a Box Enclosure International



Overview

| | |
|----------------------|--|
| Description | Specialized enclosures with integrated cooling, noise dampening, and power distribution for server and network applications in office environments. |
| Model Name | NetShelter CX 18U Secure Soundproof Server Room in a Box Enclosure International |
| Includes | Casters , Key(s) , Leveling feet , Rack Power Distribution Unit (PDU) , Side Panels , Unpacking sheet |
| Standard Lead Time | Usually in Stock |
| Product Distribution | Afghanistan , Albania , Algeria , Andorra , Angola , Armenia , Australia , Austria , Azerbaijan , Bahrain , Bangladesh , Belarus , Belgium , Benin , Bhutan , Bosnia And Herzegovina , Botswana , Brunei Darussalam , Bulgaria , Burkina Faso , Burundi , Cambodia , Cameroon , Central African Republic , Chad , China , Congo , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Cook Islands , Cote D'Ivoire , Croatia , Cyprus , Czech Republic , Denmark , Djibouti , East Timor , Egypt , Equatorial Guinea , Eritrea , Estonia , Ethiopia , Fiji , Finland , France , Gabon , Gambia , Georgia , Germany , Ghana , Gibraltar , Greece , Guadeloupe , Guinea , French Guiana , Hong Kong , Hungary , Iceland , India , Indonesia , Iran (Islamic Republic Of) , Iraq , Ireland , Israel , Italy , Jordan , Kazakhstan , Kenya , KOREA, REPUBLIC OF , Kuwait , Latvia , Lebanon , Lesotho , Liberia , Liechtenstein , Lithuania , Luxembourg , Macedonia , Madagascar , Malawi , Malaysia , Mali , Malta , Martinique , Mauritania , Mauritius , Mayotte , Moldova, Republic Of , Mongolia , Morocco , Mozambique , Myanmar , Namibia , Nepal , Netherlands , New Zealand , Niger , Nigeria , Norway , Oman , Pakistan , Papua New Guinea , Philippines , Poland , Portugal , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Senegal , Sierra Leone , Singapore , Slovakia (Slovak Republic) , Slovenia , Somalia , South Africa , Spain , Sri Lanka , Sudan , Suriname , Sweden , Switzerland , Tajikistan , TANZANIA, UNITED REPUBLIC OF , Thailand , Togo , Tunisia , Turkey , Turkmenistan , Turks And Caicos Islands , Uganda , Ukraine , United Arab Emirates , Uzbekistan , Viet Nam , Western Sahara , Yemen , Zambia , Zimbabwe |

Input

| | |
|-----------------------|------------------------------|
| Nominal Input Voltage | 200V 208V 230V 240V |
| Input Frequency | 50/60 Hz |
| Input Connections | IEC-320 C14 |

Physical

| | |
|----------------|-----------|
| Net Weight | 131.0 kg |
| Maximum Height | 1015.0 mm |
| Maximum Width | 750.0 mm |
| Maximum Depth | 1130.0 mm |

| | |
|------------------------|------------|
| Shipping Weight | 157.5 kg |
| Shipping Height | 1250.0 mm |
| Shipping Width | 800.0 mm |
| Shipping Depth | 1200.0 mm |
| Minimum Mounting Depth | 28.35 |
| Maximum Mounting Depth | 34.65 |
| Rack Height | 18 U |
| Color | Grey , Oak |
| Units per Pallet | 1.0 |

Conformance

| | |
|-------------------|--------------------------------|
| Approvals | EIA 19 Inch , TAA compliance |
| Standard warranty | 2 year (manufacturer's defect) |

Sustainable Offer Status

| | |
|-------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |