

Product data sheet

Specifications



ALTIVAR 45-2 1.1 kW-380/415V 3 phases - IP 20

ATV452VU11

⚠ Discontinued on: Dec 31, 2000

⚠ End-of-service on: Dec 31, 2005

⚠ Discontinued

Main

Range Of Product	Altivar 5
Product Or Component Type	Variable speed drive

Complementary

Product Destination	Asynchronous motors
[Us] Rated Supply Voltage	380...415 V - 15...10 %
Supply Frequency	50...60 Hz - 5...5 %
Network Frequency Limits	47.5...63 Hz
Network Number Of Phases	3 phases
Motor Power Kw	1.1 kW
Motor Power Hp	2 hp
Line Current	6 A
Continuous Output Current	4 A
Speed Drive Output Frequency	1...80 Hz
Display Type	7 segments
Output Voltage	<= power supply voltage
Physical Interface	Serial link
Height	382 mm
Width	239 mm
Depth	170 mm

Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-25...70 °C
Operating Altitude	<= 1000 m > 1000 m with current derating 3 % per 1000 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications