

# Product data sheet

Specifications



## 2HP230VATV61w/ BacNetandConduitBox

ATV61HU15M3T1BN

⚠ Discontinued on: Dec 31, 2017

⚠ End-of-service on: Oct 11, 2022

⚠ Discontinued

### Main

Asynchronous Motor Control Profile	Variable torque standard
Device Short Name	ATV61
Range Of Product	Altivar 61

### Complementary

[In] Rated Current	8 A 4.8 A 1 phase
Cable Entry	Type 1 conduit entry outdoor
Communication Port Protocol	Modbus BACnet CANopen
Input Voltage	208/240 V AC
Keypad Type	LCD keypad
Motor Power Hp	2 hp 1 hp, 1 phase
Motor Power Kw	1.5 kW 0.75 kW, 1 phase
Network Number Of Phases	3 phases output 1 phase input 3 phases

### Environment

Emc Filter	Class A EMC filter integrated
Ip Degree Of Protection	IP20
Nema Degree Of Protection	No enclosure rating (open device)
Protective Treatment	None

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	6.35 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications